




Tessi 6410 Central Shutter Lock



Description

The Tessi 6410 roller shutter lock is usually installed in the centre of the door. Both side arms extend when operated, these are linked to the shutter's locking bars, these lock the shutter into both sides of the frame for increased security. The lock case is installed on the inside of the door with the barrel protruding through the door to allow key access.



Supplied With 2 Keys



Cylinder Key



Call For Key Cutting
Services



Call For Workshop
Services

Features

- Easy to install
- Supplied with 2 keys
- Turn the key to extend the arms

Product Table

	L9388 155mm x 55mm KD
---	---------------------------------